


## CO detector CO 50

### KEY POINTS

- Easy to use
- HOLD function
- Built-in probe
- Auto shut-off: 20 minutes

### FEATURES OF THE HOUSING



**Material:** ABS

**Protection:** IP54

**Display:** 2 lines, LCD technology, 50 x 36 mm.  
1 line of 5 digits with 7 segments (value)  
1 line of 5 digits with 16 segments (unit)

**Height of digits:**  
Values: 9.2 mm  
Units: 4.7 mm

**Weight:** 200 g (with batteries)



### TECHNICAL FEATURES

| Parameter                    | Temperature                                                                 | CO                                                               |
|------------------------------|-----------------------------------------------------------------------------|------------------------------------------------------------------|
| Measuring units              | °C, °F                                                                      | ppm                                                              |
| Measuring Range              | From -20 to +80°C                                                           | From 0 to 500 ppm                                                |
| Accuracy*                    | ±0.4% of reading ±0.3°C                                                     | From 0 to 100 ppm: ±3 ppm<br>From 100 to 500 ppm: ±3% of reading |
| Resolution                   | 0.1°C                                                                       | 0.1 ppm                                                          |
| Response time                | T63 = 5 s                                                                   | T63 = 35 s                                                       |
| Measuring elements           | NTC                                                                         | Electrochemical sensor                                           |
| Conditions of use (°C/%RH/m) | From 0 to +50°C. In non-condensing conditions. From 0 to 2000 m.            |                                                                  |
| Storage temperature          | From -20 to +80°C                                                           |                                                                  |
| Power supply                 | 4 batteries AAA LR03 1.5 V                                                  |                                                                  |
| Battery life                 | 200 hours                                                                   |                                                                  |
| European directives          | 2014/30/EU EMC; 2014/35/EU Low Voltage; 2011/65/EU RoHS II; 2012/19/EU WEEE |                                                                  |

\*All the accuracies indicated in this technical datasheet were stated in laboratory conditions, and can be guaranteed for measurements carried out in the same conditions, or carried out with calibration compensation

## SUPPLIED WITH

Instruments are supplied with an adjustment certificate and a soft case.



## ACCESSORIES

- Calibration certificate
- Soft case
- Magnetic protective housing



**Only the accessories supplied with the device must be used.**



## MAINTENANCE

We carry out calibration, adjustment and maintenance of your instruments to guarantee a constant level of quality of your measurements. As part of Quality Assurance Standards, we recommend you to carry out a yearly checking.

## GUARANTEE

Instruments have 1-year guarantee for any manufacturing defect (return to our After-Sales Service required for appraisal).

## PRECAUTIONS FOR USE

Please always use the device in accordance with its intended use and within parameters described in the technical features in order not to compromise the protection ensured by the device.

## USE OF THE INSTRUMENT

### To measure CO

- Switch on the instrument by pressing briefly on **“On/Off/Hold”**.  
*The instrument displays its name “CO50” then a 5 second countdown. This count corresponds to the preheating time of the sensor. At the end of the countdown, the measured value of CO is displayed.*
- Press briefly on **“Select”** to move from CO measurement to temperature measurement.

### Hold the measurement

During measurement:

- Press briefly on **“On/Off/Hold”** to hold measurement.  
*“Hold” appears on the screen and CO and temperature measurements are fixed.*
- Press briefly on **“Select”** to move from one parameter to the other.
- Press again briefly on **“On/Off/Hold”** to exit the Hold function.

### Change the temperature unit

The instrument is on

- Pressing longer on **“Select”** to change the temperature unit.
- Press briefly on **“Select”** to select the unit: °C or °F.
- Pressing longer on **“Select”** to confirm the unit and return to the normal measuring mode.

### How to change batteries

- Remove the front part at the back of the instrument.
- Replace used batteries by new batteries AAA LR03 1.5 V.
- Replace the front.

Auto shut-off: the instrument switches off if not used during 20 minutes.



Once returned to KIMO, required waste collection will be assured in the respect of the environment in accordance with European guidelines relating to WEEE.

[www.kimo.fr](http://www.kimo.fr)

Distributed by :



EXPORT DEPARTMENT

Tel : + 33. 1. 60. 06. 69. 25 - Fax : + 33. 1. 60. 06. 69. 29

e-mail : [export@kimo.fr](mailto:export@kimo.fr)